



SCAN ME
Installation
Handbook




SCAN ME
Catalogue



SCAN ME
Website



SCAN ME
Terms and
Conditions



- Ladder Folding Platform should only be used where it is not reasonably practicable to use a platform meeting the requirements of Section 3.2.5 of Ladder Handbook.
- For use on 90 degree ladders with vertical lifelines only.
- The Fold Down Rest Platform should be stored in the up position when not in use.
- Heavy gauge aluminium for superior strength.
- FastFit ladder system is designed for single person use and rated for maximum 150kg.
- FastFit ladders are manufactured to AS 1657:2018 Standards.

COMPLETE UNIT - PRODUCT CODE: LADER002.PLT.FD

Product Code	Description	Material	Qty
LADER002.PLT.FD	Ladder Folding Platform	Aluminium	1
BOLT-M8x60mm Cup HD	Bolt: M8 x 60mm Cup Head	316SS	2
NUT M8 Flanged_316	Flanged Nut: M8	316SS	2
WASHER M8_316SS	Washer: M8	316SS	4

Ladder Examples



LADERK002.012



LADERK002.012+BASE

A FALL RESCUE PLAN SHOULD BE DEVELOPED PRIOR TO USING SAFETYLINK EQUIPMENT

© 2018, SafetyLink Pty Ltd, Australia.

Patents: SafetyLink Pty Ltd has a multitude of patents, patents pending, design applications, trademarks and copyrighted documents both lodged and issued. Should you wish to know the progress of our intellectual property on a specific product please email us on ip@safetylink.com and quote the product code.

Doc ID: MKT-1080 Version: 3.0